Crimp terminal, socket

FEATURES:

Nylon fully-insulated

Double crimp

SPECIFICATION:

Cross-section	1.5...2.5 mm²
Colour	Blue
Diameter	3.9 mm
Material	Brass
Insulation material	Nylon
Surface material	Tin-plated
Thickness	0.4 mm
Temperature range	max. +105 °C
Length	24 mm
Width	4.65 mm



Art. Nr.
RND 465-00586