

# FXX\*1)SA-K700


## e.g. F15SA-K700

\*1) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.4	25
15	39.1	24.7	33.3
25	53	38.5	47.04
37	69.3	54.9	63.5

Protection standard IP67, 100% checked according to DIN 40050

RoHS compliant

3	xx	Signal contact	S0 / Brass	AuroPur / AWG 20
2	1	Shell	Brass	tin plated
1	1	Insulator	PBT (-25°C - +70°C)	red
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
TITLE				
Measurement without tolerance				
Reference to ISO 2768-m				
SCALE 2:1				
NAME / DATE				
sschref				
DRAWN 22.05.2013				
CHECKED A.Denzinger				
22.05.2013				
 <b>fctgroup.com</b>				
REV.	1	DATE	CH.-NO.	DWG.NO.
				FXXSA-K700
				Waterproof D-Sub Miniature Connector
				REPLACEMENT FOR:
				PAGES 1