Combi CC / CoMag CC

Die kombinierten Spann- und Verschlussgeräte mit Hülse für Kompositband

Kompositband kann mit diesen Umreifungsgeräten auf einfache Weise per Hülse verschlossen werden. Somit entfällt das typische Einfädeln des Bandes in die Drahtschnalle, das manchmal als kompliziert empfunden wird.

Combi CC ermöglicht bei mittelschweren bis schweren Packgütern mit wenigen Bedienelementen das Band zu spannen und anschließend mit einer speziellen central® Hülse zuverlässig zu verschließen sowie das lose Bandende abzuschneiden.

Das integrierte Verschlusshülsenmagazin des CoMag CC ermöglicht effizientes und schnelles Umreifen, ohne jeweils eine Verschlusshülse aufzulegen. Es ist insbesondere geeignet für Packstücke mit horizontaler Auflagefläche wie Palettenware, Holzkisten, Steine und der gleichen.

- Einfacheres Verschließen von Kompositband mit Hülse anstatt mit Drahtschnalle
- Bewährtes optimales ergonomisches Arbeiten und vielseitig einsetzbar
- Hohes Spannvermögen
- Zuverlässiger flacher Krimpverschluss über spezielle central® Verschlusshülse
- Verschlussfestigkeit nahezu identisch zum Verschluss mit Drahtschnalle



The combined tensioning and sealing tools with seal for composite strap

With these manual strapping tools composite strap can be closed in a simple way. This eliminates the typically threading of the strap with wire buckle which partially is felt complicated.

At moderate to heavy goods Combi CC allows to tension the strap with few operating elements and then to close it reliably with a special central® seal as well as to cut off the loose end of the strap.

The integrated seal magazine of CoMag CC allows efficient and fast strapping without having to place a seal each time. In particular it is suitable for packages with a horizontal contact face such as goods on pallets, wooden boxes, stones and the like.

- Easier closing of composite strap with seal instead of wire buckle
- Proven optimum ergonomic working and versatile useable
- High tension capability
- Reliable flat crimp with special central® seal
- Joint strength almost identical to the closure with wire buckle

Krimpverschluss mit Hülse
Crimp seal joint

central® PET gestapelt, offen, glatt
central® PET stacked, open, even

central® PET offen, glatt
central® PET open, even

Technische Daten – Specifications

Typ Model	CC KUC	CC KUD	CC MKUC	CC MKUD
Art. Nr. Stock No.	079078	079079	079075	079076
Bandsorte Strap type	Kompositband Composite strap			
Bandbreite Strap width	13 mm (1/2“)	16 mm (5/8“)	13 mm (1/2“)	16 mm (5/8“)
Dicke Thickness	≤ 0,80 mm			
Verschluss Seal	Krimpverschluss mit Hülse Crimp seal joint			
Länge / Breite / Höhe Length / Width / Height	55 x 11 x 12 cm		58 x 11 x 16 cm	58 x 11 x 17 cm
Gewicht Weight	3,2 kg		3,7 kg	

Verschlusshülsen – Seals

Typ Type	CHUC PET	CHUD PET	MHUC PET	MHUD PET
Art. Nr. Stock No.	029806	029809	029805	029808
Abmessung Dimension	13 x 33 x 0,8 mm	16 x 33 x 0,8 mm	13 x 33 x 0,8 mm	16 x 33 x 0,8 mm
Form Shape	central® PET, offen, glatt central® PET, open, even		central® PET gestapelt, offen, glatt central® PET stacked, open, even	