Slides DZ 3832 EC-B, width 12.7 mm, up to 45 kg, full extension

Material:
Slide elements: Cold rolled steel, bright zinc-plated.
Ball retainers: Plastic / zinc-plated steel.
Balls: Hardened steel.

Telescopic precision ball bearing slides for applications in the industrial and electronics sector.
- Self Close.
- Fast Disconnect.
- Hold-in in the closed position.
- Setting cams for drawer (3.2 mm).
- Service life 80,000 cycles.
- Temperature range: +10°C to +40°C. Storage: -20°C to +80°C.

Ordering Details: e.g.: Product No. 649 015 35, Slides DZ 3832 EC-B



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	E mm	Load Rating per Pair kg	Weight per Pair kg
649 015 35	350	310	-	206	-	-	-	43	0,97
649 015 40	400	406	-	257	-	-	-	44	1,12
649 015 45	450	457	-	305	-	224	-	45	1,27
649 015 50	500	508	-	352	-	224	-	45	1,44
649 015 55	550	559	-	407	352	224	-	45	1,60
649 015 60	600	610	224	-	416	224	352	45	1,77
649 015 65	650	660	224	-	416	224	352	44	1,92
649 015 70	700	711	224	-	544	224	352	43	2,09

Note

Recommended fastening: M4 screw/4mm wood screw/6mm Euro-screw. Max. head height 2,5mm/Ø9,6mm.
Drawer width should not exceed slide length.
Use all mounting positions to achieve the max. load rating.
Horizontal mounting is not recommended.