

## Han Brid-USB 3.0-F panel feed through



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 001 2793
Specification	Han Brid-USB 3.0-F panel feed through
HARTING eCatalogue	<a href="https://b2b.harting.com/09120012793">https://b2b.harting.com/09120012793</a>

### Identification

Category	Inserts
Series	Han-Brid®
Identification	Han-Brid® USB
Specification	USB 3.0

### Version

Gender	Male
Size	3 A
Number of contacts	2
further contacts	+ USB
Details	Device side

### Technical characteristics

Rated current	1 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	$>10^{10} \Omega$
Contact resistance	$\geq 4 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$



Pushing Performance  
Since 1945

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	1
Net weight	18.2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140186682
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors