

Inset Kit LED IP44


INSET TREND KIT SW IP44 REFLED BA 36° WW DIM

3001766



Product features

- GU10 Housing with REFLED ES50 36° lamp included, Ideal for indoor application, Loop in - loop out box included



PRODUCT OVERVIEW

Product name	INSET TREND KIT SW IP44 REFLED BA 36° WW DIM
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271316
E-number SE	7467395
Warranty	3 years
Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	40
Light source included	0029126
Total power consumption (W)	4.5
Control gear type	Electronic ballast
Dimming method	Mains: leading / trailing edge
Housing colour	Aluminium
IP rating	IP44/20
IK rating	IK02
Product EAN number	8711971017660

DATA TABLE

General data

Product name	INSET TREND KIT SW IP44 REFLED BA 36° WW DIM
Technology	LED
Cap/Base	GU10

Inset Kit LED IP44

INSET TREND KIT SW IP44 REFLED BA 36° WW DIM

3001766

Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271316
E-number SE	7467395
Warranty	3 years

Optical data

Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Adjustable chromaticity	N
Beam Angle (°)	40

Electrical data

Light source included	0029126
Total power consumption (W)	4.5
Mains voltage (V)	220-240V
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	Mains: leading / trailing edge
Energy Efficiency Class (A->G) of contained light source	F

Physical data

Housing colour	Aluminium
IP rating	IP44/20
IK rating	IK02
Diffuser finish	Transparent
Diffuser material	Other
Nominal Product Height (mm)	100
Nominal Product Diameter (mm)	95
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.217
Recessed Depth (mm)	140

Packaging

Single packaging type	Carton
Product EAN number	8711971017660
Packaging single length / height (cm)	13.17
Packaging single width (cm)	10.03
Packaging single depth (cm)	8.5
DUN14 (outer)	18711971017667
Units per outer package	30

Inset Kit LED IP44

INSET TREND KIT SW IP44 REFLED BA 36° WW DIM

3001766

Packaging outer length / height (cm)	28.7
Packaging outer width (cm)	28.5
Packaging outer depth (cm)	52.9

PHOTOMETRY

TECHNICAL DRAWINGS

