


## Sylproof Superia LED G3 fixed output SYLPROOF SUPERIA LED G3 600mm Twin 4K 0048690



### Product features

- Sylproof Superia, integrated LED weatherproof luminaire, with UV stabilized flat diffuser and linear prisms designed to achieve uniform lit appearance, optimise light output and to reduce glare, stainless steel diffuser clips and fixing brackets for surface and wall mounting. GRP housing, Polycarbonate diffuser, Non dimmable, 4000K, CRI80, 2700 lm, 19 W, 140 lm/W, nominal average life (h):50000, energy class: A++ A+ A Class I, IK08, IP65.



### PRODUCT OVERVIEW

Product name	SYLPROOF SUPERIA LED G3 600mm Twin 4K
Technology	LED
Housing	Polyester
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC000109
Warranty	5 years
Fixture luminous flux (lm)	2700
Luminaire efficacy (lm/W)	140
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	100
Photobiological Risk Group	RG0
Total power consumption (W)	19
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288486901

### DATA TABLE

#### General data

Product name	SYLPROOF SUPERIA LED G3 600mm Twin 4K
Technology	LED
Housing	Polyester

## Sylproof Superia LED G3 fixed output

*SYLPROOF SUPERIA LED G3 600mm Twin 4K*  
0048690

Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC000109
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	2700
Luminaire efficacy (lm/W)	140
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	100
Photobiological Risk Group	RG0

### Electrical data

Total power consumption (W)	19
Mains voltage (V)	220-240V
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
Control gear required	No
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Drive current (mA)	300
Inrush Current (A)	4
Inrush Duration (µs)	32
Glow Wire Test (°C)	850
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	70
Max. Luminaires per 13A C Breaker	90
Max. Luminaires per 16A C Breaker	110
Max. Luminaires per 20A C Breaker	140
Max. Luminaires per 10A B Breaker	60
Max. Luminaires per 13A B Breaker	80
Max. Luminaires per 16A B Breaker	100
Max. Luminaires per 20A B Breaker	125

### Lifetime data

Lifespan L70 B50	60000
Lifespan L80 B10	60000
Lifespan L90 B50	60000

## Sylproof Superia LED G3 fixed output SYLPROOF SUPERIA LED G3 600mm Twin 4K 0048690

### Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	665
Nominal Product Width (mm)	110
Nominal Product Height (mm)	78
Weight (kg)	1.18


### Packaging

Single packaging type	Carton
Product EAN number	5410288486901
Packaging single length / height (cm)	77.5
Packaging single width (cm)	11.6
Packaging single depth (cm)	8.4
DUN14 (outer)	05410288486901
Units per outer package	1
Packaging outer length / height (cm)	77.5
Packaging outer width (cm)	11.6
Packaging outer depth (cm)	8.4

### Safety data

Optimal operating condition (°C)	-20-40
Dry applications use only	No

## PHOTOMETRY



## TECHNICAL DRAWINGS

