

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form

Art. no.	26195 090
Type	standard
Nominal dimension of groove	22 mm
Slot nut width	21.7 mm
Thread dimension	M20
Length	35 mm
Height	28 mm
Slot nut height	14 mm
DIN	508



EAN-Code

4020772080082