

## Electronic workshop vernier callipers

TWIN-CAL, IP67, with blade tips

 **TESA**

### Application:

For measuring external and internal dimensions.

### Execution:

- ON
- Zero setting at any position
- mm/inch switch-over
- Auto off
- ABS function
- With blade tips for external dimensions

### Advantage:

- IP protection guaranteed even with data transfer connection
- Soft Touch for comfortable handling

### Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



|   |                    |
|---|--------------------|
| <b>Art. no.</b>                                   | <b>31154 281</b>   |
| <b>Brand</b>                                      | TESA               |
| <b>Manufacturer Part Number</b>                   | 00530436           |
| <b>Min./max. length measuring range</b>           | 0-800 mm           |
| <b>Data transmission type</b>                     | TLC                |
| <b>IP protection class</b>                        | IP 67              |
| <b>Length of jaw</b>                              | 150 mm             |
| <b>Measuring tips</b>                             | Yes                |
| <b>Fine adjustment</b>                            | No                 |
| <b>Digit increment</b>                            | 0.01 mm            |
| <b>Inner measurement scales</b>                   | 20 mm              |
| <b>Type of locating</b>                           | With locking screw |
| <b>Display</b>                                    | Digital            |
| <b>Calibration Group</b>                          | A                  |
| <b>Number of rechargeable batteries/batteries</b> | 1 PCS              |
| <b>Battery designation</b>                        | 3V CR2032 Lithium  |
| <b>ISO</b>  | 13385-1            |
| <b>Gross Weight</b>                               | 4.500 kg           |
| <b>Product Group</b>                              | 362                |

### EAN

7630041106466