

Electronic micrometer

With large measuring range IP65

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65

Advantage:

- Long battery life, approx. 2.4 years
- IP65

Delivery:

Includes box, wrench, battery, setting standard (from 25 mm), up to 50-mm measuring range with factory test certificate



Art. no.	32017 438
Brand	MITUTOYO
Manufacturer Part Number	293-254-30
Display	Digital
Min./max. length measuring range	200-225 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Hold-function (AE lock), Origin (Dimension preset), Preset function, Automatic switch-off
Min./max. measurement force	5-10 N
Error limit	3 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	126 mm
Measuring spindle increments	0.5 mm
Calibration Group	D, E
Gross Weight	2.340 kg
Product Group	3MA

EAN

4946368695464