

# PB770-25286

## UGREEN 48000mAh 300W Fast Charging Power Bank



### Features

- **Lightning-Fast Charging:** Charge up to 300W, with PD3.1 140W bi-directional charging. Get your devices juiced up in no time.
- **Long-Lasting Power:** A whopping 48,000mAh capacity means 10.8 iPhone 15 Pro charges or 1.1 MacBook Air M2 15 charges. Perfect for long trips, meetings, or outdoor adventures
- **Safe & Durable:** Automotive-grade LiFePO4 batteries ensure superior safety and longevity. After 3,000 cycles, still retains over 80% capacity.
- **Practical Design:** LED light with 3 modes (high, low, SOS) for any occasion. Lightweight, compact, and comes with a carrying handle, smart display, and non-slip mat.

### Specifications

- \*USB-C1 Input: 140W Max
- \*USB-C1 Output: 140W Max, USB-C2 Output: 100W Max, USB-C3 Output: 100W Max
- \*USB-A1 Output: 22.5W Max, USB-A2 Output: 22.5W Max
- \*Multi-port Output(USB-C1+USB-C2+USB-C3): 300W Max
- \*Total Output: 5V=9A/9V=3A/12V=3A/15V=3A/20V=5A
- \*Output Capacity: 23000mAh (5v/9A),14000mAh (9v/9A ),10500mAh(12v/9A),8500mAh(15V/9A) 6300mAh (20V/15A Max),4500mAh (28V/5A Max)
- \*Digital Display
- \*Multiple protection, Superior Safety
- \*Charging Time: About 2 hours (with PD3.1 140w Charger)
- \*Cell Capacity: 48000mAh(6000mAhx8pcs)
- \*Rated Energy: 153.6wh(25.6V 6000mAh)
- \*Rated Capacity: 23000mAh (TYP 5V 9A)
- \*Dimensions:L145.3xW77xH106.3(mm)/L5.7xW3.0xH4.2 (inch)