


# E12090



## Connection cable

VSTGN040ZDS0002L04STGP080--S



### Application

Special feature	Screened cable
Design	Ethernet cable, D-coded
Application	cross-over patch cable; patch cable

### Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67; IP 20; (M12 plug / RJ45 plug)

### Mechanical data

Weight	[g]	166.7
Materials		TPU / PA
Material nut		diecast zinc, nickel-plated

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection - plug M12

Connector: 1 x M12, straight; Moulded body: PA; Locking: diecast zinc, nickel-plated; Tightening torque: 0.7...0.9 Nm



# E12090




## Connection cable

VSTGN040ZDS0002L04STGP080--S

### Electrical connection

Cable: 2 m, PVC, green,  $\varnothing$  6.5 mm, shielded; 2 x 2 x 0.38 mm<sup>2</sup>

### Connection



### Electrical connection - plug RJ45

Connector: 1 x RJ45, straight; Moulded body: TPU

