




CABLE CAN ADAPTER

Connection technology



L: 0.15 m

Product characteristics

Jumper

M12 plug / M12 socket

CAN adapter cable: M12 plug, 5-pole / M12 socket, 8-pole

Gold-plated contacts

Electrical data

Electrical design

AC/DC

Operating voltage [V]

30 AC / 36 DC

Current rating [A]

4

Environment

Ambient temperature [°C]

-30...80

Protection

IP 68

Mechanical data

Design

straight / straight

Material body

PUR

Material nut

Brass; nickel-plated

Weight [kg]

0.049

Electrical connection




Connection

PUR / PVC cable / 0.15 m; 4 x 0.25 mm²; Ø 6.8 mm

Sheath colour

black

Wiring



Remarks

Pack quantity

[piece]

1