


**SOLID PC 1919 18 G**



Sample photo

**Order symbol:** PC 1919 18 G  
**Product nbr:** 5330369  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074005427  
**EI. number:**  
 Finland: 3423703  
 Electric No. Italy: 7401015  
 Electric No. Sweden: 2539408

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

| Dimensions: | Length | Width | Height | Accessories: |                         |
|-------------|--------|-------|--------|--------------|-------------------------|
| mm:         | 188    | 188   | 180    | EKHXT        | Mounting plate isolated |
| inch:       | 7.4    | 7.4   | 7.1    | EKV 12       | DIN-35 Mounting rail    |

| Materials:                    |                      | Rating:                                     |
|-------------------------------|----------------------|---|
| <b>Material:</b>              | Polycarbonate        | Ingress Protection (EN 60529): IP66/IP67    |
| <b>Base colour:</b>           | RAL 7035 -light grey | Impact Resistance (EN 62262): IK08/IK09     |
| <b>Cover screws material:</b> | Polyamide            | Electrical insulation: Totally insulated    |
| <b>Cover colour:</b>          | RAL 7035 -light grey | Halogen free (DIN/VDE 0472, Part 815): 1    |
| <b>Cover screws colour:</b>   | Grey                 | UV resistance: UL 508                       |
| <b>Gasket material:</b>       | Polyurethane         | Flammability Rating: UL 746C 5"             |
|                               |                      | Glow Wire Test (IEC 695-2-1) °C: 960        |
|                               |                      | NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12 |

| Temperatures:                       |                | Certificates: |
|-------------------------------------|----------------|---------------|
| <b>Temperature °C (short term):</b> | -40 ... 120 °C | SGS Fimko     |
| <b>Temperature °C (continuous):</b> | -40 ... 80 °C  |               |
| <b>Temperature °F (short term):</b> | -40 ... 250 °F |               |
| <b>Temperature °F (continuous):</b> | -40 ... 175 °F |               |

| Accessories: |                |
|--------------|----------------|
| EKHVT        | Mounting plate |

