


## Myriad V IP65 White Bezel

MYRIAD IP65 4000K ELE WHITE  
2050671



### Product features

- MYRIAD IP65 4000K ELE WHITE



## PRODUCT OVERVIEW

Product name	MYRIAD IP65 4000K ELE WHITE
Technology	LED
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Retail
ETIM Class	EC001744
E-number SE	7462012
E-number Norway	3290236
Warranty	5 years
Fixture luminous flux (lm)	1050
Luminaire efficacy (lm/W)	105
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Beam Angle (°)	30
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimming method	N/A
Housing colour	White
IP rating	IP65/20
IK rating	IK02
Product EAN number	5025768506712

## DATA TABLE

### General data

Product name	MYRIAD IP65 4000K ELE WHITE
--------------	-----------------------------

## Myriad V IP65 White Bezel

*MYRIAD IP65 4000K ELE WHITE*  
2050671

Technology	LED
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number SE	7462012
E-number Norway	3290236
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	1050
Luminaire efficacy (lm/W)	105
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Adjustable chromaticity	N
Beam Angle (°)	30
Distribution type	Adjustable
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	10
Mains voltage (V)	230V
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Integral
Transformer required	Yes
Dimming method	N/A
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B10	50000
------------------	-------

### Physical data

Housing colour	White
IP rating	IP65/20
IK rating	IK02
Diffuser material	Glass
Nominal Product Length (mm)	76
Nominal Product Width (mm)	76
Nominal Product Height (mm)	72
Nominal Product Diameter (mm)	76
Cutout Dimensions (W x L in mm or Diameter in mm)	76


## Myriad V IP65 White Bezel MYRIAD IP65 4000K ELE WHITE 2050671

Max. Lamp Diameter (mm) - D	76
Weight (kg)	0.39
Recessed Depth (mm)	72

### Packaging

Single packaging type	Carton
Product EAN number	5025768506712
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

### PHOTOMETRY



Distance [m]	Cone diameter [m]	E(0°) E(C0)	14.8°	Illuminance [lx]
0.5	0.26	838	229	
1.0	0.53	129	50	
1.5	0.79	80	23	
2.0	1.06	315	142	
2.5	1.32	202	91	
3.0	1.59	140	63	

Distance [m] Cone diameter [m] Illuminance [lx]  
C0 - C180 (Half beam angle: 29.8°)

### TECHNICAL DRAWINGS

