

PORTWEST®

PRODUCT SPECIFICATION & TECHNICAL DATA

FW64 - STEELITE™ TREKKER SHOE S1P

EN ISO 20345:2004 + A1:2007

- Features:
- Antistatic footwear
 - CE certified
 - Dual density sole unit
 - Energy absorbing seat region
 - Oil resistant outsole
 - Steel midsole
 - 200 Joule steel toecap
 - Slip resistant outsole (SRC)
 - Puncture resistant steel midsole (PR)
 - Protective steel toecap - impact (I), compression (C)



Description: Breathable, strong and flexible style. Steel toecap, midsole and oil resistant outsole will give you peace of mind when working.

Box Qty: 12

Commodity Code: 6403400000

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m³)	EAN13	DUN14
FW64BKR36	Black	63.0	47.0	37.0	1.3400	0.1096	5036108203499	15036108692160
FW64BKR37	Black	63.0	47.0	37.0	1.3800	0.1096	5036108164752	15036108630803
FW64BKR38	Black	93.0	47.0	37.0	1.4000	0.1617	5036108164769	15036108630810
FW64BKR39	Black	63.0	47.0	37.0	1.4200	0.1096	5036108164776	15036108630827
FW64BKR40	Black	63.0	47.0	37.0	1.4400	0.1096	5036108164783	15036108630834
FW64BKR41	Black	63.0	47.0	37.0	1.4600	0.1096	5036108164790	15036108630841
FW64BKR42	Black	66.0	49.0	37.0	1.4800	0.1197	5036108164806	15036108630858
FW64BKR43	Black	66.0	49.0	37.0	1.5000	0.1197	5036108164813	15036108630865
FW64BKR44	Black	66.0	49.0	37.0	1.5200	0.1197	5036108164820	15036108630872
FW64BKR45	Black	69.0	51.0	37.0	1.5400	0.1302	5036108164837	15036108630889
FW64BKR46	Black	69.0	51.0	37.0	1.5800	0.1302	5036108164844	15036108630896
FW64BKR47	Black	69.0	51.0	37.0	1.6000	0.1302	5036108164851	15036108630902
FW64BKR48	Black	69.0	51.0	37.0	1.6200	0.1302	5036108203505	15036108692177