

## Ergonomic WG series workbench with manual height adjustment

Solid beechwood 1500 mm, 3 drawers with full extension, height-adjustable by crank handle

### Execution:

- Continuous height adjustment from approx. 740-1040 mm via hand crank (removable)
- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, with level compensation on all four feet

### Advantage:

- Workbench can be quickly and easily adjusted to the desired working height
- Always working at the right height ensures ideal ergonomic conditions
- When you buy this product, you plant a tree and also receive a tree certificate!

### Delivery:

Fully assembled including hand crank



<b>Art. no.</b>	<b>50212 334</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50212334
<b>Number of drawers</b>	3 PCS
<b>Worktop width</b>	1500 mm
<b>Worktop height</b>	50 mm
<b>Pullout type</b>	Full extension
<b>Worktop depth</b>	700 mm
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Functions</b>	RFID possible
<b>Max. height</b>	1040 mm
<b>Min. height</b>	740 mm
<b>Adjustable in height</b>	Yes
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>With single pull-out safety brake</b>	Yes
<b>Surface</b>	Powder-coated
<b>Load-carrying capacity</b>	800 kg
<b>Drawer front height</b>	1 x 90 mm, 2 x 120 mm
<b>Type</b>	Manual height adjustment
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	450 x 600 mm
<b>Material of worktop</b>	Solid beech
<b>Material of base frame</b>	Steel plate
<b>Drawer width (inner dimension)</b>	450 mm
<b>Drawer depth (inner dimension)</b>	600 mm
<b>Levelling</b>	Yes
<b>Load-carrying capacity per drawer</b>	70 kg
<b>Dynamic load-carrying capacity</b>	200 kg
<b>Central locking</b>	Yes
<b>Gross Weight</b>	130.000 kg
<b>Product Group</b>	5BC

### EAN

4053625048960