





5.08X(N-1)+16.4



2EDG - DBM - 5.08 - XXP - 1Y - 00A (H)
 (Series No.) (Pitch) (Poles) (Single Pitch)
 00A-(Standard) (Color):1: (RoHS)

- 1. (Blue)
- 2. (Grey)
- 3. (Black)
- 4. (Green)
- 5. (Orange)
- 6. (Red)
- 7. (Transparent)
- 8. (Yellow)
- 9. (White)

NOTES1:

- UL Standard
- 1. Rated voltage/current : 300V / 15A
- 2. Withstanding voltage : AC1600V/1Min.
- 3. Torque value : M3 , 5.31lb.in
- 4. Wire range : 28~12AWG

1.

Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(kV)	4.0K	4.0KV	4.0KV
Rate voltage(V)	630V	320V	250V
Rate current(A)	12A		


- 2. Torque value : M3 , 0.6N·m
- 3. Wire range : 0.2~2.5mm²

NOTES2:

- 1. Dimension shall be interpreted per ASME Y14.5-2009
- 2. Pitch : 5.08mm, Poles : N=02P~24P
- 3. Stripping length : 7~8mm
- 4. Operating temperature: -40C~+105C
- 5. Undimensioned tolerances:


Pitch range in mm	Nominal dimension range			mm
	Over	Over	Over	
TO	6	10	TO	150
6	10	24	30	150
F0.15	F0.20	F0.30	F0.50	F0.70
F1.00	F1.30	F1.50	F2.00	F2.50

6. RoHS Compliance




DETACHED LISTS

PART NO.:	/	NAME:	DEGSON [®] NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司	
APPD:	/	CHKD:	/	
DFTI:	/	TITLE:	CUSTOMER DRAWING	REV
		DRAWING NO.:	/	DO
				SHEET
				SCALE



THIRD ANGLE PROJECTION



DO NOT SCALE DRAWING SCALE 1:1