



Product Information

Product Category	REFRIGERATION
Unit Barcode	5016368079959
Outer Carton Barcode	
Commodity Code	8418402099
Country of Origin	CHINA
Primary Colour	WHITE
Finish	STAINLESS STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	156.4
Rated Current	0.68
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	1.7
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	1420	550	550
Packaged Dimensions H x W x D (mm)	1450	585	585
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			40
Unit Packaged Weight (Kg)			44
Carton Weight (Kg)			
EPS (Kg)	0.618	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.248	Card / Paper (Kg)	2.708
Aluminium (Kg)		Steel (Kg)	

Category Specific Technical Information

Type	OTHER REFRIGERATING APPLIANCE	Number of Freezer Compartments	5
Design Type	FREESTANDING	Number of Fridge Shelves	
Gross Total Volume	160	Door Hinge Position	
Net Total Volume	160	Reversible Door	YES
Net Refrigeration Volume		Door Handle Colour	STAINLESS STEEL
Net Freezing Volume	160	Door Handle Material	PLASTIC
Energy Efficiency Index	124.7	Door Material	METAL
Energy Rating	F	Door Opening Angle	135
Airborne Acoustical Noise Emission Class		Housing Colour	WHITE
Annual Energy Consumption	235	Lamp Rated Power	
Climate Class	N/ST	LED Lighting	NO
Minimum Ambient Operating Temperature	16	Power Failure Safe Storage	
Maximum Ambient Operating Temperature	38	Temperature Rise Time	9
Winter Setting	NO	Thermostat Temperature Range	-24~-12
Freezer Star Rating	4	Thermostat Type	MECHANICAL
Fast Freeze Facility	NO	Refrigerant Type	R600A
Freezing Capacity	7.2	Refrigerant Amount	54
Defrosting Type	M	RF: Back Panel Material	FULL METAL
Freezer Technology	STATIC		