

**Q - MAX PUNCHES    METRIC**

| <b>PUNCH SIZE</b> | <b>BOLT SIZE</b> |  |
|-------------------|------------------|--|
| 10mm              | 6 m/m x 40       |  |
| 11mm              | 6 m/m x 40       |  |
| 12.7mm            | 8 m/m x 40       |  |
| 14mm              | 8 m/m x 40       |  |
| 15mm              | 8 m/m x 30       |  |
| 16mm              | 8 m/m x 30       |  |
| 17.5mm            | 8 m/m x 30       |  |
| 18.6mm            | 10 m/m x 35      |  |
| 19mm              | 10 m/m x 35      |  |
| 20mm              | 10 m/m x 35      |  |
| 20.4mm            | 10 m/m x 35      |  |
| 21mm              | 10 m/m x 35      |  |
| 22.5mm            | 10 m/m x 45      |  |
| 24mm              | 10 m/m x 45      |  |
| 25mm              | 10 m/m x 45      |  |
| 27.5mm            | 10 m/m x 45      |  |
| 28.3mm            | 10 m/m x 45      |  |
| 29mm              | 10 m/m x 45      |  |
| 30mm              | 10 m/m x 45      |  |
| 31mm              | 10 m/m x 45      |  |
| 32.5mm            | 12 m/m x 45      |  |
| 34mm              | 12 m/m x 45      |  |
| 35mm              | 12 m/m x 45      |  |
| 37mm              | 12 m/m x 50      |  |
| 37.5mm            | 12 m/m x 50      |  |
| 40mm              | 12 m/m x 50      |  |
| 45mm              | 12 m/m x 50      |  |
| 47mm              | 12 m/m x 50      |  |
| 48mm              | 12 m/m x 50      |  |
| 50mm              | 12 m/m x 50      |  |
| 51mm              | 12 m/m x 50      |  |
| 52mm              | 16 m/m x 60      |  |
| 54mm              | 16 m/m x 60      |  |
| 55mm              | 16 m/m x 60      |  |
| 60mm              | 16 m/m x 60      |  |
| 64mm              | 16 m/m x 65      |  |
| 65mm              | 16 m/m x 65      |  |
| 70mm              | 16 m/m x 65      |  |
| 75mm              | 16 m/m x 65      |  |
| 76.5mm            | 16 m/m x 70      |  |
| 80mm              | 16 m/m x 70      |  |
|                   |                  |  |
|                   |                  |  |
|                   |                  |  |

