

CONNECTING PLUG FOR SIMATIC HMI KP32F PN 24 PIN, 24V DC, 4 PIECES PER PACKAGING UNIT



Product type designation	
Installation type/mounting	
Wall mounting/direct mounting possible	Yes; can be plugged into SIMATIC HMI device
Supply voltage	
Rated value (DC)	24 V; DC
Interfaces	
Number of pins HMI-side	24; Female
Number of pins device-side	24; Female, spring-loaded terminals 0.75 mm ²
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	95 %
Mechanics/material	
Type of housing (front)	
• plastic	Yes

Dimensions	
Width	16 mm
Height	54 mm
Thickness	20 mm
Scope of supply	
Delivery unit in items	4; Without ejector
other	
Note:	for KP32F PN
Usable in the following products	
<ul style="list-style-type: none"> Product 1 	6AV3688-3EH47-0AX0
last modified:	12.03.2015