



## Orthomat® Ultimate

The ultimate foam mat to reduce fatigue - do your worst!



- When you need the lightness of foam but the resilience of a nitrile mat.
- Soft inner layer cushions impact from standing to reduce fatigue or discomfort.
- Unique outer layer encapsulates entire mat to prevent moisture ingress.
- Edges are heat sealed for outstanding durability.
- High density composition gives extra support and shape recovery.
- Ramped edges limit trip risk.
- Textured surface provides traction and captures some dirt and swarf.
- Fire tested to BS EN 13501-1.

### Parts

Part Number	Size	Colour	Weight
OU010001	0.6 m x 0.9 m	Black	2.92 kg
OU010002	0.9 m x 1.5 m	Black	7.29 kg
OU010003	0.9 m x 18.3 m	Black	89.00 kg
OU010003C	0.9 m x per linear metre (max. 18.3 m)	Black	3.00 kg

### Technical Specification

<b>Material</b>	Open Cell PVC (Foam) with PolyNit outer (fusion bonded, not glued)
<b>Surface Finish</b>	Pyramid pattern
<b>Product Height</b>	15 mm
<b>Roll Length</b>	18.3 m
<b>Operating Temperature</b>	0°C to +55°C
<b>Resistance to Chemicals</b>	In tests conducted by COBA, Orthomat® Ultimate showed no visible signs of corrosion or damage when fully submerged in both of the following chemicals: Castrol Alpha SP 320 Industrial Extreme Pressure Gear Oil and Pac 89 Phosphoric Acid Cleaner
<b>Environmental Resistance</b>	Suitable for wet and dry indoor environments
<b>Typical Applications</b>	Demanding locations e.g. Engineering workshops
<b>Installation Method</b>	Loose lay
<b>Cleaning Method</b>	Brush/mop the top surface
<b>Fire Tested to</b>	BS EN 13501-1 Class Cfl - s1

## Technical Specification

<b>Country of Origin</b>	China
--------------------------	-------

---

<b>Guarantee</b>	3 years
------------------	---------

---

Get in touch | To order FREE samples or arrange a site visit please call +44 (0)116 240 1088 or email [sales@cobaeurope.com](mailto:sales@cobaeurope.com)