

HP w1907 19-inch widescreen flat panel monitor with BrightView Panel

Datasheet



Stylish Design for Home Entertainment or Home Office

- Wide viewing angle makes it easy to adjust the monitor easily for work and play
- Maximize desk space with innovative features such as integrated speakers, keyboard parking space and Easy Clip by attaching on photo and flower holders to your monitor
- Get a high quality widescreen picture with a Brightview panel and high contrast ratio



The HP w1907 is an attractive and sensible design with amazing graphics and video quality.

- The HP w1907 features a BrightView wide panel for brilliant picture quality.
- HDCP-enabled for optimum viewing of High Definition content (High-Bandwidth Digital Content Protection)
- My Display provides one touch adjustment for brightness, color and contrast
- Quick View modes change work environments easily and quickly
- Dual inputs support digital (DVI-D) and analog (VGA) signals.
- The widescreen provides more space to work and play
- Wide aspect ratio and fast response time bring gaming, videos and the internet brilliantly alive when you plug into your HP PC
- Swivel monitor easily from side-to-side when sharing the screen
- Personalize your monitor with Easy Clip by clipping on photo holders, cameras, and accessories
- With a resolution of 1440 x 900 and a wide workspace you have what you need to watch a video, edit photos, surf the net or play a game on your PC
- Work easily between multiple software windows, extra wide spreadsheets or on two-page layouts with less scrolling.
- Dual inputs support true digital (DVI-D) and traditional analog (VGA) signals.
- Integrated speakers keep your desktop clutter-free
- Park your keyboard in the convenient space under the monitor when not in use

High Resolution Picture Quality and Ultimate flexibility

- Creative and technical users can maximize project productivity with this wide screen. View two pages side by side for editing graphic layouts, or working with wider spread sheets.
- Extreme resolution at 1440 x 900 for bright, awesome graphic quality perfect for multimedia viewing, photo editing or gaming on your PC
- Standard 15-pin D-sub analog and advanced DVI-D digital interface with HDCP for optimal graphic performance

Easy to Use

- Less need to scroll side to side with the wide view
- Wide screen provides space to keep small windows like calendars, post its etc on the side.
- Wide viewing angle for multi-viewer applications
- Large, on-screen picture with digital user controls for custom tuning
- Plug and play for quick and easy installation, no drivers required

Award winning support from HP

- Buy any HP product and you get more than just great technology. You the get the peace of mind of HP's award-winning product help and support
- Enjoy the benefits of Total Care. 24/7 access online and off. Prompt service-real time chat with a support technician and as fast as one-hour email responses.
- Direct knowledgeable assistance by phone, agents in English and Spanish in US, or English or French in Canada. 1-800-HPINVENT (or insert regional phone numbers)

Additional Information

- HP makes it easy to recycle PCs, monitors and peripherals, any brand or manufacturer. Reduce, reuse and recycle. www.hp.com/recycle

HP w1907 19-inch widescreen flat panel monitor with BrightView Panel

Datasheet

Monitor Specifications

LCD Panel Type	• 19" diagonal Widescreen Thin-Film Transistor LCD active matrix
Native Resolution (recommended)	• 1440 x 900 @ 60 Hz
Contrast Ratio (typical)	• 1000:1 (typical)
Brightness (typical)	• 300 nits (typical)
Pixel Pitch	• 0.285 mm
Response Time (typical)	• 5 ms (on-off)
Signal Input Connectors	• VGA and DVI-D connections and HDCP VGA and DVI cables included
Resolution Formats	• 640 x 480 @ 60 Hz, 70 Hz, 75 Hz • 720 x 400 @ 70 Hz • 800 x 600 @ 60 Hz, 75 Hz • 832 x 624 @ 75 Hz • 1024 x 768 @ 60 Hz, 75 Hz • 1152 x 720 @ 60 Hz • 1152 x 870 @ 75 Hz • 1152 x 900 @ 65 Hz • 1280 x 768 @ 60 Hz • 1280 x 960 @ 60 Hz • 1280 x 1024 @ 60 Hz, 75 Hz • 1440 x 900 @ 60 Hz
Power Supply	• Internal AC Adapter
Maximum Power Rating	• <49 W
Energy Saving Mode	• <2 W in sleep mode
Tilt	• -5 to +25 degrees
Detachable Base	• Yes
VESA Mounting	• Standard 4 hole pattern 100 mm x 100 mm screw-mounting option; pedestal is removable
Dimensions Unpacked	• 18.2"(h) x 14.9"(w) x 7.2"(d) (46.2 x 38.0 x 18.4 cm)
Weight Unpacked	• 11.0 lbs (5.0 Kg)
Dimensions Packed	• 6.4"(h) x 19.2"(w) x 21.1"(d) (16.3 x 48.9 x 53.6 cm)
Weight Packed	• 15.0 lbs (6.8 Kg)
Languages	• English • German • French • Spanish • Italian • Dutch • Simplified Chinese • Japanese

Energy Star Compliant • Yes

Speaker Specifications

Type	• Integrated Rear Facing
Output Power	• 2 w x 2

Accessories, Warranty and Agency Approvals

Supplied Accessories	• A/C power cable 6.2 ft (1.9m) • VGA cables 4.9 ft (1.5m) • Audio Cable • DVI Cable 5.9 ft (1.9m) • Documentation CD • Limited Warranty Card
-----------------------------	--

Agency Approvals	• 9241-3,7,8 VDT guidelines • ISO 13406-2 pixel defect guidelines • MPR-II • CISPR • VCCI • CSA (Canada) • ACA (Australia) • BSMI (Taiwan) • CCC (China) • MIC (South Korea) • NOM (Mexico) • CE Marking • FCC approval, • Energy Star • Microsoft® Windows® certified (Microsoft Windows 2000, Microsoft Windows XP and Microsoft Vista) • UL listed • GOST (Russia) • SASO (Saudi Arabia) • SABS (South Africa) • BNCI • Argentina • SEMKO
-------------------------	---

Limited Warranty	• Limited 1 year warranty. Availability varies by region. Certain restrictions and exclusions apply.
-------------------------	--

Visit www.hp.com for more details!

*All specifications represent the typical specifications provided by HP's component manufacturers.

Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing shall be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ©2007 Hewlett-Packard Development Company, L.P. 09/05/07_r4 sl Product Number: RK283AA #ABA

