

SOLID PC 1919 18 T



Sample photo

Order symbol: PC 1919 18 T
Product nbr: 5330069
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005410
EI. number:
 Finland: 3423803
 Electric No. Italy: 7402015
 Electric No. Sweden: 2539438

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	188	188	180	EKHXT	Mounting plate isolated
inch:	7.4	7.4	7.1	EKV 12	DIN-35 Mounting rail

Materials:		Rating:
Material:	Polycarbonate	Ingress Protection (EN 60529): IP66/IP67
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08/IK09
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	Clear transparent	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey	UV resistance: UL 508
Gasket material:	Polyurethane	Flammability Rating: UL 746C 5"
		Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:		Certificates:
Temperature °C (short term):	-40 ... 120 °C	SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C	Gost R
Temperature °F (short term):	-40 ... 250 °F	
Temperature °F (continuous):	-40 ... 175 °F	

Accessories:	
EKHVT	Mounting plate

