UL1569 Style Stranded Hook-Up Wire







RoHS Compliant

This stranded Hook-Up Wire meets the specifications of UL AWM/Style 1569 - 105°C / 300V. UL recognized (UL file no. E352035).


Specifications

Conductor Material : Stranded Tinned Copper

Insulator Material : PVC
Rated Temperature : 105°C
Rated Voltage : 300V

Cable Length : Available in 305m Reel or in per metre length

Diagram



Marking



Length

AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Insulation Colour	Part Number
16	65/0.16	1.49	2.3	14.6	Black	PP002543
					Brown	PP002371
					Red	PP002544
					Yellow	PP002373
					Green/Yellow	PP002545
					Blue	PP002370
					White	PP002372
	34/0.18	1.21	2	23.2	Black	PP002546
18					Brown	PP002547
					Red	PP002548
					Orange	PP002377
					Yellow	PP002550
					Green/Yellow	PP002376
					Green	PP002375
					Blue	PP002374

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk



UL1569 Style Stranded Hook-Up Wire



AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Insulation Colour	Part Number
40	0.4/0.40	1.04		22.0	Purple	PP002378
18	34/0.18	1.21	2	23.2	White	PP002549
	21/0.18	0.95	1.8	36.7	Black	PP002551
					Brown	PP002379
20					Red	PP002552
					Orange	PP002381
					Green	PP002380
					Blue	PP002553
					Purple	PP002383
					Grey	PP002382
					White	PP002384
					Black	PP002554
					Brown	PP002385
		0.76			Red	PP002556
					Orange	PP002388
	17/0.16		1.6	59.4	Yellow	PP002558
22					Green/Yellow	PP002387
					Green	PP002386
					Blue	PP002555
					Purple	PP002390
					Grey	PP002389
					White	PP002557
	11/0.16	0.61	1.4	94.2	Black	PP002559
					Brown	PP002391
					Red	PP002562
					Orange	PP002561
					Yellow	PP002564
24					Green/Yellow	PP002393
					Green	PP002392
					Blue	PP002560
					Purple	PP002395
					Grey	PP002394
					White	PP002563
	7/0.16	0.49	1.3	150	Black	PP002565
00					Brown	PP002397
26					Red	PP002566
					Orange	PP002399

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk



UL1569 Style Stranded Hook-Up Wire



AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Insulation Colour	Part Number
26	7/0.16	0.49	1.3	150	Yellow	PP002402
					Green	PP002398
					Blue	PP002396
					Grey	PP002400
					White	PP002401
28	7/0.127	0.39	1.2	237.25	Black	PP002403
					Brown	PP002405
					Red	PP002407
					Yellow	PP002409
					Green	PP002406
					Blue	PP002404
					White	PP002408
	7/0.10	0.31	1.1	381	Black	PP002410
30					Brown	PP002412
					Red	PP002414
					Yellow	PP002416
					Green	PP002413
					Blue	PP002411
					White	PP002415

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

