


Part number

# CGMA 25



## Brief description:

100A CG contacts, silver plated, 25mmq, AWG 4-3

Product description		Approvals / Standards	
Model	male contacts	Quality mark	 DNV GL, BV, EAC
Version	Crimp contacts CLASS series	Conformity	CQC, CE
Series	100A CG contacts	<b>General ordering information</b>	
Family	crimp contacts	EAN13 code	8015747122702
N. of poles	1 pole	Tariff number	85369095
Technical data		Packaging Information	
Current	100 A	Packaging length	132,00 mm
Wire cross-section	25,00 mm <sup>2</sup>	Packaging height	108,00 mm
AWG size	4 - 3	Packaging width	210,00 mm
Contact type	silver plated	Packaging weight	3,56 kg
Further technical details		Packaging volume	2,99 dm <sup>3</sup>
Weight	20,00 g	Packaging description	Carton box
		Packaging quantity	150 Pcs
		Packaging EAN code	8015747225588
		Sub-packaging length	1,00 mm
		Sub-packaging height	1,00 mm
		Sub-packaging width	1,00 mm
		Sub-packaging weight	0,71 kg
		Sub-packaging description	Plastic box
		Sub-packaging quantity	30 Pcs
		Sub-packaging EAN barcode	8015747122733

Part number

# CGMA 25



Catalogue drawings

## CGF and CGM

