

Cordless circular saw bench TS 36-18 LTX BL 254

With base and trolley function

metabo

Execution:

- Integrated dust extraction with cyclone for low-dust work without vacuum
- Quickly switch between floor-level and standing sawing thanks to integrated, retractable frame
- Ring gear guide for precise saw blade inclination
- Finely adjustable parallel stop with double clamping and quick attachment
- Saw blade swivel range: -1.5 to 46.5 degrees
- Working height 850/355 mm
- Max. material width 200 mm at angle stop

Advantage:

- Extra-large work area thanks to pull-out table length and width extensions
- Splitting wedge can be retracted without tools for concealed cuts and transport
- All mounting parts can be attached to the housing for compact transport and storage

Delivery:

Not including battery pack or charger, cemented carbide saw blade with alternating teeth (40 teeth), fabric dust bag, base, rubber wheels, parallel stop, angle stop, table extension, table width extension, push stick, dust cyclone



Art. no.	71169 432
Model	TS 36-18 LTX BL 254
Battery voltage	18 V
Battery included	No
Number of rechargeable batteries/batteries	0
Functions	Soft start, Overloading protection, Restarting protection, Extraction possible, Engine brake
Saw blade diameter	254 mm
Drill hole	30 mm
Width of support plate	970 mm
Support plate length	995 mm
Motor design	Brushless motor
Cutting speed	66 m/s
Min./max. cutting height	0-87 mm
Max. cutting width	630 mm
Weight	34.5 kg
Idle speed	5000 rpm
With soft start	Yes
Product Group	Prod. Gr. 745

EAN

4007430321602