

## Spring balances with load capacity of 2.0-14.0 kg, with automatic lock

Type 7222, cable extension 3000 mm, rustproof

**AUTOSTAT**

### Application:

Can be used for the following tools and devices, e.g.: Electrical and compressed air hand machines, engravers, exhaust hoses, compressed air devices, paint spray guns, film welding devices

### Advantage:

- Effortless work



<b>Art. no.</b>	<b>77001 572</b>
<b>Brand</b>	AUTOSTAT
<b>Manufacturer Part Number</b>	77001572
<b>Min. load-carrying capacity</b>	2 kg
<b>Max. load-carrying capacity</b>	5 kg
<b>Type</b>	7222
<b>With automatic locking</b>	Yes
<b>Max. cable pull-out length</b>	3000 mm
<b>Adjustable cord length</b>	No
<b>Material of cord</b>	Stainless Steel
<b>Wire cable diameter</b>	3 mm
<b>Replaceable cord</b>	Yes
<b>Cord in-feed restriction</b>	Absorbs impacts, adjustable
<b>Material of cable drum</b>	Abrasion-proof plastic
<b>Suspension type</b>	Freely rotating and pivot screw karabiner hook
<b>Load attachment</b>	Screw Karabiner hook
<b>Material of housing</b>	Plastic
<b>Housing height</b>	259.4 mm
<b>Housing width</b>	211.5 mm
<b>Housing thickness</b>	70 mm
<b>Design</b>	All external components made of non-rusting material
<b>Height</b>	550 mm
<b>Spring design</b>	Special mainspring
<b>With overrotation protection</b>	Yes
<b>Spring breakage protection</b>	Yes
<b>Number of springs</b>	1 PCS
<b>DIN</b>	15112
<b>Gross Weight</b>	3.500 kg
<b>Product Group</b>	7EB

### EAN

4053625360161