

Ring bolt

Screwable sling point, 360° rotation

CARTEC

Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing



Art. no.	77232 112
Brand	CARTEC
Manufacturer Part Number	C807XHT12
Design	Without key
Thread dimension	M12
Load-carrying capacity	0.75 t
Distance between lower edge of retainer holder and retainer	41.5 mm
Bracket width	11.5 mm
Bracket height	12.5 mm
Outer diameter	55.5 mm
Diameter 2	36.5 mm
Internal width	30 mm
Width of support plate	30.6 mm
Usable thread length	18 mm
Width across flats	8 mm
Weight	0.2 kg
Gross Weight	0.231 kg
Product Group	775

EAN

8013429916045