


Montagebohrung / panel piercing



Außenleiter / outer conductor	Messing / brass	vernickelt / Nickel plated
Kontaktstift / contact pin	Messing / brass	vergoldet / Gold plated
Isolierung / insulator	POM	
Crimprohr / crimp ferrule	Messing / brass	vernickelt / Nickel plated
sonstige Metallteile / other metal parts	Messing / brass	vernickelt / Nickel plated

Kabel / cable

G7: RG-174/U; RG-188A/U; RG-316/U
KX 22A; KX 3B

Ⓐ Montage / assembly

B2828 Ⓑ

c	12461	05.04.01	BJ	97	Datum/date	Name/name	Werkstoff/ material
	b	12401	15.03.01	BJ	gez./drawn	07.07.	SN
	a	8088	15.07.97	BJ	gepr./appr.	08.07.97	BJ
					Norm/stand.		
				Maßstab/scale	Benennung/title		
				2:1	Mini-UHF-Kabeleinbaubuchse Mini-UHF Bulkhead Receptacle		
				untol. Maße/ dim. without tolerances according to	Untert./doc.type	Zeichnungsnr./drawing no.	
				K	J01046F0003		
				Ersatz für/ replaces	EW970043-00		
				Telegärtner			Maße/dimensions: mm
							Original: DIN A4