


E10750



Damping magnet

Magnet M2.0/Alnico



Operating conditions

Ambient temperature	[°C]	-100...450
---------------------	------	------------

Mechanical data

Weight	[g]	6.2
Dimensions	[mm]	Ø 6 / L = 25
Materials		AlNiCo
Magnetic field strength	[mT]	101

Remarks

Pack quantity		1 pcs.
---------------	--	--------