

# c **FL**<sup>®</sup>US

## **Model Number**


#### V15S-G-PG9

Cable connector, M12, 5-pin, ready for assembly

#### **Features**

- · Screw terminal connection
- Metal locking

### **Dimensions**



Technical data		
General specifications		
Number of pins		5
Connection 1		Male connector
Construction type 1		straight
Threading 1		M12
UL File Number		E363587
Electrical specifications		
Operating voltage L	J <sub>B</sub>	max. 125 V AC/DC
Operating current		max. 4 A
Volume resistance		< 8 mΩ
Ambient conditions		
Ambient temperature		-40 85 °C (-40 185 °F)
Pollution Degree		3
Mechanical specifications		
Degree of protection		IP67
Connection		1 x M12 connector, straight Screw terminals for max. 0.75 mm <sup>2</sup> PG9 cable gland
Material		
Contacts		CuZn
Contact surface		CuSnZn
Body		PA
Cable		
Sheath diameter		6 8 mm
Mating cycles		100
Compliance with standards and distives	rec-	
Standard conformity		
Degree of protection		EN 60529:2000

#### **Electrical connection**

