

ROLINE DesignSecure 1200

Product No.	19.40.1212
Manufacturer	ROLINE
Manufacturer No.	19.40.1212
EAN (single piece)	7611990976768



- Compact designed UPS in futuristic design
- For Workstations and PCs
- LineInteractive UPS
- AVR (Automatic Voltage Regulation)
- Digital status display
- Integrated overvoltage protection
- Telephone/Modem connections
- USB Port for advanced Power Management Software (incl. in content of delivery)
- EMI/RFI Noise Filter
- Dimensions (HxLxW) 168 x 105 x 334 mm
- Weight: 6.3 kg
- Backup Time: up to 4 Minutes

Technical specifications

Manufacturer	ROLINE
Product group	UPS
Product type	UPS Line Interactive
Colour	black /silver
Scope of delivery	UPS, Software, Cable Set
Classification (IEC 62040-3)	VI-SS-333

UPS technology	Line Interactive
Power class	1000 ... 1900 VA
Output (VA/W)	1200/720
Backup time	3 min
Backup time full/half-load	3 / 6 min
Weight	14 kg
Dimensions (HxWxD)	168 x 105 x 334 mm
Mounting form	Turm
Voltage (input)	230 V
Voltage (output)	230 V
Output voltage regulation	yes
Frequency	50 Hz
Connector type (input)	cold connector IEC320 C14
Outputs	4
Connector type (output)	4 cold connector IEC320 C13
Phase in/output	230V/230V / 50Hz
Over current protection	EMI,- RFI-Filter
Max. quantity of delay expansion units	0
Delay expansion unit	--
Slots for adapter card	0
Slot for adapter card	--
Interface	USB
USB 2.0 Interface	Yes
Hot swap batteries	No
Bypass	No
Additional over current protector	Telephone/Fax
Activity	Display

Activity LED	--
Activity Display	yes
incl.Management Software	Windows
Internal cooling	Passive
Ambient temperature	0-40 °C

Backup Time

Capacity (VA / W)	minutes
200/120	40
400/240	18
600/360	9
800/480	5
1000/600	3,5
1200/720	2,5