


# ROLINE UTP Patch Cord, Cat.6, yellow, 3.0 m

<b>Product No.</b>	21.15.1552
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	21.15.1552
<b>EAN (single piece)</b>	7611990156368



Patch cable for networking connections between devices. Prepared unshielded Twisted Pair cable with RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded copper wire.

For a structured cabling system we recommend to use the following components: ROLINE Cat.6 UTP Cable, Solid Wire, AWG23: 21.15.0990 (100 m), 21.15.0991 (300 m); ROLINE Cat.6 Flush Mount Wall Jack, unshielded: 25.16.8494 (white), 25.16.8500 (ivory); ROLINE Cat.6 Surface Mount Wall Jack, unshielded: 25.16.8394 (white), 25.16.8395 (ivory); ROLINE Cat.6 19" Patch Panel, 24 Ports, unshielded: 26.11.0355 (light grey), 26.11.0362 (black); ROLINE Cat.6 UTP Patch Cord, grey, 5 m: 21.15.0935. The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2329b-10-E (with flush mount)/z2330b-10-E (with surface mount).

## Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable

Product type	UTP Patch Cables
--------------	------------------

Colour	yellow
--------	--------

Length	3 m
--------	-----

Shield type	UTP
-------------	-----

Transfer quality	Cat6 / Class E
------------------	----------------

Impedance	100 Ohm
-----------	---------

Quantity of wires	8
-------------------	---

Conductor type	Wire
----------------	------

Crossed	No
---------	----

Colour (Spout)	yellow
----------------	--------

Cable LSOH	No
------------	----

Connector Type RJ45	Standard
---------------------	----------