

Slides DZ 9308, Width 19.1 mm, to 227 kg, Full Extension

Material:

Slide elements: Cold-rolled steel, bright zinc-plated.
Ball retainers: Plastic.
Balls: Hardened steel.

Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Slides sold separately (left or right).
- Lock-in in open position.
- Lock-out in closed position.
- Front lever lock release.
- Only for vertical mounting.
- Optional bracket accessory kits for various mounting options (page 630).
- Service life 10,000 cycles (to 180 kg up to 75,000 cycles).
- Temperature range: -20°C to +70°C.


Note: Sold singly.
Picture: Left slide.



Accuride

Ordering details: e.g.: Prod. No. 649 052 12, Slide DZ 9308, left
Prod. No. 649 054 12, Slide DZ 9308, right

Drawing: Left Slide



Product No. per Piece left	Product No. per Piece right	Slide Length mm	Travel +/-3.3 mm	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm	K mm	M mm	N mm	P mm	Q mm	R mm	Load Rating per Pair kg	Weight per Piece kg
649 052 12	649 054 12	305	305	-	-	-	-	-	153,9	179,3	198,4	-	-	-	203,2	260,4	279,4	227	1,46
649 052 14	649 054 14	356	356	-	-	-	-	-	204,7	230,1	249,2	-	-	-	254,0	311,2	330,2	227	1,71
649 052 16	649 054 16	406	406	-	-	-	-	-	255,5	280,9	300,0	-	-	-	304,8	362,0	381,0	227	1,97
649 052 18	649 054 18	457	457	127	-	-	-	-	306,3	331,7	350,8	-	-	-	355,6	412,8	431,8	227	2,21
649 052 20	649 054 20	508	508	127	-	-	-	296,9	357,1	382,5	401,6	-	-	-	406,4	463,6	482,6	227	2,45
649 052 22	649 054 22	559	559	127	190,5	-	-	347,7	407,9	433,3	452,4	-	-	-	457,2	514,4	533,4	227	2,69
649 052 24	649 054 24	610	610	127	190,5	-	-	398,5	458,7	484,1	503,2	-	-	-	508,0	565,2	584,2	227	2,96
649 052 26	649 054 26	660	660	127	190,5	-	-	449,3	509,5	534,9	554,0	-	-	-	558,8	616,0	635,0	227	3,20
649 052 28	649 054 28	711	711	127	190,5	-	-	500,1	560,3	585,7	604,8	-	-	-	609,6	666,8	685,8	227	3,46
649 052 30	649 054 30	762	762	127	190,5	-	-	550,9	611,1	636,5	655,6	235	-	501,7	660,4	717,6	736,6	222	3,71
649 052 32	649 054 32	813	813	127	190,5	-	-	601,7	661,9	687,3	706,4	235	-	552,5	711,2	768,4	787,4	218	3,98
649 052 34	649 054 34	864	864	127	190,5	-	520,7	652,5	712,7	738,1	757,1	235	-	-	762,0	819,1	832,2	213	4,22
649 052 36	649 054 36	914	914	127	190,5	368,3	520,7	703,3	763,5	788,9	807,9	235	-	-	812,8	869,9	889,0	209	4,49
649 052 40	649 054 40	1016	1016	127	190,5	368,3	-	804,9	865,1	890,5	909,5	235	-	755,7	914,4	971,5	990,6	200	5,03
649 052 42	649 054 42	1067	1067	127	190,5	368,3	-	855,7	915,7	941,3	960,4	235	-	806,5	965,2	1022,4	1041,4	195	5,27
649 052 48	649 054 48	1219	1219	127	190,5	368,3	520,7	1008,1	1068,3	1093,7	1112,8	235	-	958,9	1117,6	1174,8	1193,8	182	6,00
649 052 60	649 054 60	1524	1524	127	190,5	368,3	520,7	1312,9	1373,1	1398,5	1417,8	235	596,9	958,9	1422,4	1479,5	1498,6	154	7,54

Note

These slides are sold separately. To lock both sides a left-hand and a right-hand slide are required. To lock one side a left or right-hand slide can be combined with slide DZ 9301-E as non-locking companion slide, see page 626.

Attention: Vertical mounting only.

Recommended mount: M5/M6 screw.

Max. screw head of 4.8 mm height and 12.7 mm Ø.

Use all mounting positions to achieve the max. load rating.

Bracket accessory kits DZ 634 for side and bottom mounting see page 630.