



## HY433/12 NY

12 pole natural polyamide PA6.6 pillar terminal block 10mm pitch 32a 450v



### SPECIFICATION

<b>Number of Poles</b>	12
<b>Terminal Material</b>	OT58 nickel plated
<b>Body Material</b>	Polyamide PA6.6
<b>Colour</b>	Natural
<b>Glow Wire Resistance Test Temp</b>	GWIT775°C (EN60695-2-13)
<b>Max Conductor Size (Sq mm)</b>	4
<b>Max Current (A)</b>	32
<b>Max Voltage (V)</b>	450
<b>Working Temperature</b>	110
<b>Pitch (mm)</b>	10
<b>Height (mm)</b>	17.6
<b>Width (mm)</b>	20.2
<b>Length (mm)</b>	116.7
<b>Diameter (mm)</b>	3.2
<b>Flammability Rating</b>	UL94V2 and GWIT775°C
<b>Terminal Screw Material</b>	White zinc plated steel