

PACF29CO W

12NC: 859991643590

GTIN (EAN) code: 8003437629525

Whirlpool

SENSING THE DIFFERENCE



- Type: Portables
- BTU cooling capacity: 9000
- Energy class cooling: A
- Main colour of product: White
- 6th Sense
- Sleep mode
- Jet function
- Around U function
- Dehumidification function
- Filter type: Washable
- Temperature display (°C): Yes
- Remote control: Yes
- Cooling sound power value for Indoor unit: 60
- EER Cooling: 2.6
- Refrigerant gas type: R290
- Container Loading Capacity (20'/40'/40'HQ): 134/284/425
- Gross weight (kg): 37
- Net weight (kg): 33.3
- Dimensions Indoor unit HxWxD: 718x442x326 mm
- Depth packed Indoor unit: 386
- Gross weight Indoor unit: 35
- Net weight Indoor unit: 31

Whirlpool air conditioner - PACF29CO W

This Whirlpool freestanding air-conditioner features: energy efficiency class A. White color. Portable air conditioner, to easily move your air conditioner wherever you need. On/Off cool. 6th SENSE, the temperature sensor automatically evaluates the temperature of the room and makes the ideal combination of the operational functions in order to get the best comfort ever.



Low noise level: 60dbA

With a noise level of 60dbA, this air conditioner guarantees a calm and quite ambient so that you can enjoy your relaxing moments to the fullest.



Autoclean Function

Your Air Conditioner is preventing the growth of harmful micro-organisms, thanks to AutoClean function drying out the moisture inside the product keeping it dry and clean.



Jet Cooling Function

Thanks to Jet Cooling Function this product is the perfect ally to restore the ideal temperature in your room, quickly. - 5°C in just 10 minutes* as you don't have to wait to fully enjoy your well-being at home. * Jet cooling: Referred to PACF212CO W portable model with Jet function. Test condition settings: indoor temperature 30°C, room size 13.9m2.



9000 BTU

9000 BTU cooling capacity, recommended for rooms of 14.5 - 17 m2.



Compact Design

Modern design, very easy to move from one room to the other thanks to the wheels.



Sleep mode - Portable

Thanks to Sleep Mode the led panel will turn off at night to avoid any disturbance as you can enjoy a comfortable sleep.



Dehumidification function

You can now easily and quickly manage the humidity level, feeling more comfortable when it is very hot or cold, thanks to the Dehumidification function, removing more than 2L of water from the room in 1 hour*. *Referred to PACF212CO W portable model with dry function. Test condition settings: indoor temperature 30°C with 80% humidity, room size 13.3m2.



6TH SENSE Technology

Thanks to the temperature sensor, the unique 6th sense technology can automatically select the operating mode that is more suitable for you.

PACF29CO W

12NC: 859991643590

GTIN (EAN) code: 8003437629525

Whirlpool

SENSING THE DIFFERENCE

DIMENSIONS

Current (A)	4,7
Frequency (Hz)	50
Depth IDU	326
Depth packed IDU	386
Gross weight IDU	35
Height IDU	718
Height packed IDU	885
Net weight IDU	31
Width IDU	442
Width packed IDU	498

TECHNICAL FEATURES

Auto defrost	No
Dehumidification function	Yes
Room temperature display	Yes
Refrigerant gas type	R290

PERFORMANCES

Energy class cooling	A
Energy class heating	N/A
Annual energy consumption during cooling season - kWh/annum	0
Annual energy consumption during heating season average (Green) - kWh/annum	0
Capacity Range Cooling Max	0
Capacity Range Cooling Min	0
Capacity Range Heating Max	0
Capacity Range Heating Min	0
Cooling sound power value for IDU	60
COP Heating	0
Declared capacity (kW)	0
EER Cooling	2.6
Heating sound power value for IDU	0
Rated capacity heating (kW)	0
Sound pressure noise level IDU - Silent mode	0
Working T° Range Cooling - Indoor range	21°C - 35°C
Working T° Range Cooling - Outdoor range	N/A
Working T° Range Heating - Indoor range	N/A
Working T° Range Heating - Outdoor range	N/A
Max current Cooling	4.8
Max current Heating	0