

shrink-fit extensions with IC

with straight shank

ATORN[®]

Application

For extending and reducing to smaller diameters.

Version

- With 4.5 ° angle
- Clamping diameter for shaft tolerance h 6
- Workpiece stop screw with 10 mm adjustment travel



Art. No.	23431 640
Clamping diameter	14 mm
Outer diameter	25 mm
Tapered diameter	20 mm
Length	150 mm
Max. clamp in depth	47 mm
Min. clamp in depth	37 mm
Max. adjustment travel	10 mm
Setting screw size	M10 x 1 mm
Width across flats	5 mm

EAN-Code

40502934 18217