

Micrometer

ISOMASTER

 **TESA**

Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force

Delivery:

In a case, test report with declaration of conformity



Art. no.	31366 050
Brand	TESA
Manufacturer Part Number	00110103
Min./max. length measuring range	50-75 mm
Vernier scale	0.01 mm
Measuring surface diameter	6.5 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Display	Nonius
DIN	863
Calibration Group	D
Gross Weight	0.800 kg
Product Group	362

EAN

7630041104103