

## Electronic depth caliper

Series 571 with hook IP67

Mitutoyo

### Application:

For measuring e.g. Drilling depths, distances to workpieces etc.

### Execution:

- ORIGIN (absolute zero)
- Digimatic data output
- IP67
- Automatic deactivation after 20 minutes of non-utilisation
- With bores in the measuring bridge for connecting interchangeable measuring bridges (separate accessories)
- Depth gauge in hook version

### Advantage:

- OFFSET (pressing the Offset button compensates the width of the hook)

### Delivery:

In a case, including 1x SR44 battery



<b>Art. no.</b>	<b>32018 264</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	571-264-20
<b>Min./max. length measuring range</b>	0-150 mm
<b>Min./max. length measuring range in inches</b>	0-6 in
<b>Data transmission type</b>	DIGIMATIC
<b>Digit increment</b>	0.01 mm
<b>Error limit</b>	0.03 mm
<b>IP protection class</b>	IP 67
<b>Bridge length x bridge width</b>	250 x 10 mm
<b>Type of locating</b>	With locking screw
<b>Calibration Group</b>	B
<b>With automatic shut off</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Display</b>	Digital
<b>Battery designation</b>	1,5 V SR44
<b>Bridge length</b>	250 mm
<b>Functions</b>	ABS function, Absolute function, Automatic switch-off, Origin (Dimension preset), On/Off
<b>With drive wheel</b>	No
<b>With ABS function</b>	Yes
<b>With mm / inch switching</b>	Yes
<b>Gross Weight</b>	0.236 kg
<b>Product Group</b>	3MA

### EAN

4946368727202