

## Sack truck with sliding handles and vertical struts

Load capacity up to 250 kg, solid rubber tyres

**fetra**  
Transportgeräte

### Execution:

- From steel pipe with steel sheet toe plate
- Sturdy welded structure
- Screwed-on toe plate can be exchanged
- Wheels with plastic rims and roller bearings
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant

### Delivery:

Flat-packed



<b>Art. no.</b>	<b>50270 314</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	B1116V
<b>Toe plate width</b>	480 mm
<b>Height</b>	1150 mm
<b>Design</b>	With vertical bar
<b>Toe plate depth</b>	300 mm
<b>Load-carrying capacity</b>	250 kg
<b>Width</b>	590 mm
<b>Surface</b>	Powder-coated
<b>Wheel diameter</b>	250 mm
<b>Material</b>	Steel pipe
<b>Material of wheel</b>	Solid rubber
<b>Total stop optional</b>	No
<b>Gross Weight</b>	17.500 kg
<b>Product Group</b>	5AB

### EAN

4017976111162