



Bemerkung:

Werkstoff: Polyamid GV, schwarz
Längentoleranz: 0,10 mm



Art.-Nr.	SW	L	Zoll	C1/C2	G1/G2	PG	ab Lager	ab x Stück	*
7030-5	6	5		5/5	M3/M3	95	Ja		
7030-6	6	6		6/6	M3/M3	96	Ja		
7030-6	6	6		7/7	M3/M3	96	Ja		
7030-8	6	8		8/8	M3/M3	96	Ja		
7030-9	6	9		9/9	M3/M3	97	Ja		
7030-10	6	10		10/10	M3/M3	97	Ja		
7030-11	6	11		11/11	M3/M3	99	Ja		
7030-12	6	12		12/12	M3/M3	99	Ja		
7030-13	6	13		13/13	M3/M3	102	Ja		
7030-14	6	14		14/14	M3/M3	102	Ja		
7030-15	6	15		15/15	M3/M3	102	Ja		
7030-16	6	16		8/8	M3/M3	104	Ja		
7030-17	6	17		8/8	M3/M3	104	Ja		
7030-18	6	18		8/8	M3/M3	104	Ja		
7030-19	6	19		8/8	M3/M3	104	Ja		
7030-20	6	20		10/10	M3/M3	104	Ja		
7030-21	6	21		10/10	M3/M3	125	Ja		
7030-22	6	22		10/10	M3/M3	125	Ja		
7030-23	6	23		10/10	M3/M3	125	Ja		
7030-24	6	24		10/10	M3/M3	125	Ja		
7030-25	6	25		10/10	M3/M3	125	Ja		
7030-26	6	26		10/10	M3/M3	129	Ja		
7030-27	6	27		10/10	M3/M3	129	Ja		
7030-28	6	28		10/10	M3/M3	129	Ja		
7030-29	6	29		10/10	M3/M3	129	Ja		
7030-30	6	30		10/10	M3/M3	129	Ja		
7030-31	6	31		10/10	M3/M3	131	Ja		
7030-32	6	32		10/10	M3/M3	131	Ja		
7030-33	6	33		10/10	M3/M3	131	Ja		
7030-34	6	34		10/10	M3/M3	131	Ja		

Art.-Nr.	SW	L	Zoll	C1/C2	G1/G2	PG	ab Lager	ab x Stück	*
7030-35	6	35		10/10	M3/M3	131	Ja		
7030-36	6	36		10/10	M3/M3	133	Ja		
7030-37	6	37		10/10	M3/M3	133	Ja		
7030-38	6	38		10/10	M3/M3	133	Ja		
7030-39	6	39		10/10	M3/M3	133	Ja		
7030-40	6	40		10/10	M3/M3	133	Ja		
7030-41	6	41		10/10	M3/M3	134	Ja		
7030-42	6	42		10/10	M3/M3	134	Ja		
7030-43	6	43		10/10	M3/M3	134	Ja		
7030-44	6	44		10/10	M3/M3	134	Ja		
7030-45	6	45		10/10	M3/M3	134	Ja		
7030-46	6	46		10/10	M3/M3	136	Ja		
7030-47	6	47		10/10	M3/M3	136	Ja		
7030-48	6	48		10/10	M3/M3	136	Ja		
7030-49	6	49		10/10	M3/M3	136	Ja		
7030-50	6	50		10/10	M3/M3	136	Ja		
7030-55	6	55		10/10	M3/M3	145	Ja		
7030-60	6	60		10/10	M3/M3	149	Ja		