

NYS373-*

Phono plug, black shell, gold plated contacts, rubber boot for best antikink protection, chuck type strain relief for cable O.D. 3.5 to 6.1 mm, color coding ring

*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue, 9-White



Image gallery



Technical Information [▼hide](#)

Product

Title NYS373-*

Electrical

Dielectric strength 0.5 kVdc

Insulation resistance $\geq 1 \text{ G}\Omega$

Rated current depends on mated connector

Contact resistance depends on mated connector

Mechanical

Cable O.D. 3.5 - 6.1 mm

Lifetime > 1000 mating cycles

Wiresize 24 AWG

Material

Insulation Thermoplastic

Strain relief Internal plastic chuck

Environmental

Temperature range -25 °C to +70 °C