

80106 Penetration probe Ø3.0mm, L=130mm

General

Application	Process measurement
Construction	Sharp Point thermocouple
Handgrip	ABS plastic



Sensor

Thermocouple	Type K
Nauwkeurigheid	Volgens IEC 584-1
Responsietijd	12 seconds
Max. tip temperatuur	600°C / 1112°F

Sensor

Materiaal	Stainless steel
Tip diameter	3 mm
Probe length	130 mm

Cable

Aansluitkabel	Coiled cable, polyurethane insulated
Kabellengte	1000 mm
Type	K
Color	Black
Connector	Miniature thermocouple connector, flat pins

Options

Kabel kleur	IEC / ANSI
Connector kleur	IEC / ANSI

