

# PRODUCT SPECIFICATION

<b>Brand</b>	KASP
<b>Product Range</b>	Steel padlocks
<b>Catalogue number</b>	180
<b>Date</b>	18/01/2008

## Range Description

Open and Close shackle steel padlocks

## Features

- Hardened steel shackle – extra protection from hacksaw and cropping attacks
- Double ball bearing locking mechanism – extra strength to resist torsion and pull attacks
- Chrome plated steel body – extra strength & resistance to corrosion
- 5 Pin cylinder featuring paracentric keyway and anti pick mushroom pins for extra protection against picking
- The close shackle version offers additional shackle protection to resist shackle attack

Both padlocks are supplied display packed, in sealed blister packs.

2 Keys are supplied with each padlock



Technical product information	<p><b>Body</b> - Steel, Chrome plated</p> <p><b>Shackle</b>- Hardened steel, Chrome plated</p> <p><b>Locking mechanism</b>- Pin tumbler cylinder type, 5 pin cylinder, Brass pins – Driver pin 5 is plain, driver pins 1 to 4 are mushroom type.</p> <p><b>Key differs</b>- 1988</p> <p><b>Re-keyable</b> – Yes</p> <p><b>Security rating:</b></p> <table><tr><td>Type</td><td>Security rating</td></tr><tr><td>K18060</td><td>11</td></tr><tr><td>K18060X</td><td>13</td></tr></table> <p><b>Shackle Dimensions:</b></p> <table><tr><td></td><td colspan="3">Shackle</td><td>Body</td></tr><tr><td>Dimensions mm</td><td>Dia</td><td>Internal width</td><td>Internal height</td><td>Width</td></tr><tr><td>K18060</td><td>12</td><td>34</td><td>28</td><td>60</td></tr><tr><td>K18060X</td><td>12</td><td>35</td><td>27</td><td>60</td></tr></table> <p><b>Use environment</b>- Normal outdoor use</p> <p><b>Recommended applications</b>- Garages, Shutters, Vehicles and Site gates</p>	Type	Security rating	K18060	11	K18060X	13		Shackle			Body	Dimensions mm	Dia	Internal width	Internal height	Width	K18060	12	34	28	60	K18060X	12	35	27	60
Type	Security rating																										
K18060	11																										
K18060X	13																										
	Shackle			Body																							
Dimensions mm	Dia	Internal width	Internal height	Width																							
K18060	12	34	28	60																							
K18060X	12	35	27	60																							
Standards compliance	None applicable																										
User health and safety information	None applicable																										
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations																										
Material safety data	None applicable																										
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered																										
Country of origin	China																										

## Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K18060D	60	27	98	628	150	35	190	696
K18060XD	60	27	98	726	150	35	190	797
K18060KB	23	3	54	10	–	–	–	–
K18060	60	27	98	628	70	115	40	680
K18060X	60	27	98	726	70	115	40	770
K18060KA	60	27	98	628	70	115	40	680
K18060XKA	60	27	98	726	70	115	40	770
K16080MK	60	27	98	628	70	115	40	680
K16080XMK	60	27	98	726	70	115	40	770