

MAGNET COIL F. CONTACTORS 7,5KW AC 440 V, 60 HZ FOR MOTOR CONTACTORS SZ S0, SCREW TERMINAL










General technical data:

product brand name		SIRIUS
Product designation		Magnet coil

Control circuit:

Type of voltage of the control supply voltage		AC
Apparent power loss of the magnet coil with AC typical	V·A	7.6
Control supply voltage <ul style="list-style-type: none"> • 1 with AC <ul style="list-style-type: none"> — at 50 Hz Rated value 	V	440
Operating range factor control supply voltage rated value of the magnet coil with AC <ul style="list-style-type: none"> • at 50 Hz • at 60 Hz 		0.8 ... 1.1 0.85 ... 1.1

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval		
	 EG-Konf.	Special Test Certificate	 ABS	 BUREAU VERITAS	 DNV
Shipping Approval	other				
 GL	 LRS	 RMRS	Confirmation	Environmental Confirmations	 VDE

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT29245AR11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RT29245AR11/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RT29245AR11&lang=en>

last modified:

09.03.2015