

EK EKOE 130 G



Sample photo

Order symbol: EKOE 130 G
Product nbr: 2538037
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013569
EI. number:
 Finland: 3425418
 Electric No. Italy: 7501040
 Electric No. Sweden: 2538037

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	280	280	130	EKO 30-G	Cover
inch:	11.0	11.0	5.1	EKO 80-G	Cover
				EKO 30-T	Cover
				EKO 80-T	Cover

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

EKOVT	Mounting plate
EKOXT	Mounting plate isolated
EKV 22	DIN-35 Mounting rail
EKOZR	Extension frame

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Accessories:	
EKOE	Base, PC

Certificates:
Germanischer Lloyd (GL)
SGS Fimko
Lloyds Register of Shipping (LR)
Gost R

