




PTFE Exposed Welded Tip Thermocouples with Plug



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Thermocouple types K, J & T
- Fast response, welded exposed junction
- 2 or 3 metre long PTFE insulated twin-twisted lead
- 1/0.2mm conductors
- 'Re-Wireable' miniature flat pin plug
- Temperature range -75°C to $+250^{\circ}\text{C}$
- Tolerance to IEC 584 Class 1
- Colour code to IEC 584-3
- Ideal for test & development applications
- Available in packs of 5, or single packs

T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire	Farnell order code
'K'	1/0.2mm	2 metre	Mini plug	Green	White	859-8185(pack of 5)
'K'	1/0.2mm	3 metre	Mini plug	Green	White	163-3490
'J'	1/0.2mm	2 metre	Mini plug	Black	White	859-8215(pack of 5)
'J'	1/0.2mm	3 metre	Mini plug	Black	White	163-3489
'T'	1/0.2mm	2 metre	Mini plug	Brown	White	859-8193(pack of 5)
'T'	1/0.2mm	3 metre	Mini plug	Brown	White	163-3492

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com