




**SPECIFICATION  
CONTROL DRAWING  
Crystal Resonator**

**FREQUENCY**  
**19.200000MHz**



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 20PPM at 25°C
Temperature Stability	± 20 PPM
Operating Temp. Range	-10°C to +60°C
Load Capacitance	12 pF
ESR	50 Max Ohm
Drive Level	100uW Max mW
Static Capacitance (C0)	Unspecified pF
Ageing	+/-5ppm 1st Year Max
Marking	AEL19.2 WWYY

Amdt Date	Change Note	AEL Code
		<b>X19M200000S015</b>
		<b>Issue Ref</b> A