

Product data sheet

Item No. 92.232.5014.1

Cable assembly GST18I3K1-S 15W 50SW

geis® Connection cable male - free end; length: 5m; type GST18I3; 3-pole; 250 V / 16 A; colour of coding: black with black strain-relief; cable: H05V2V2-F 3G1,5, colour: black



Item No.	92.232.5014.1
EAN	4015573692169
Order Unit	20 Piece(s)

Certificates / Approvals

Technical data

**General**

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

**Model**

Number of poles	3
Nominal cross section conductor	1.5 mm <sup>2</sup>
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05V2V2-F
Cable colour	Black
Cable diameter	8.3 mm

Version of cable	Male - free end
Type of cord set	Connection cable
Version cable end 1	GST18i3 plug
Version cable end 2	Free end

**Material**

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	90 °C
Insulation components continuous temperature	100 °C

**Dimensions**

Total length	5 m
--------------	-----